

8XA Inductor Measurements

Detailed measurements of gapped cores, and methodologies for measuring, the 8XA inductor.

- 2000 Permeability EC52 core
- 4200 Permeability EC52 E Core

2000 Permeability EC52 core

The following test results were performed using a 2000 permeability EC52/24/14 core purchased from Mouser Electronics. Please see the link below for the exact core.

[Mouser Electronics_EC52/24/14_N27OL](#)

TDK's document covered the core material. 2000 permeability is listed within attached documentation.

[TDK N27 Core Datasheet](#)

image-1656072489879.png

Image not found or type unknown

EC52/24/14 are the dimensions in mm. EC52 is called out in the component values given from Stan's estate data as seen below.

image-1656072073655.png

Image not found or type unknown

According to the above values, the inductance measured was 720uH per coil.

This being a bifilar coil, only one set needs measured. The replication winding methodology for this coil is covered by Max Miller in the below YouTube link. Please reference it to understand how the coils are wrapped.

[Irondmax How To Wind A 8XA ECore](#)

In the video, Max Miller mentions needing to gap the core. This reference is based off photos from Stan's estate provided by Don Gable. Below is a picture showing Stan's original gapped E core.

image-1656072716383.png

Image not found or type unknown

An LC meter was purchased to measure the values of inductances with precision plastic shims used for gapping. Plastic was selected to avoid any ferromagnetic materials affecting measurements.

Model number: LC100-A

Part Number: 021311199

image-1656072992165.png

Image not found or type unknown

The meter was tested with a known inductor purchased from Digikey. 33uH rating. Meter measured 35uH. This was acceptable for the measurements. To get a more precise measurement, a function generator and oscilloscope could be utilized. Below are the values of different gapping distances using the shims. Please note, that these are preliminary measurements. A better methodology is being worked on and will be available at a later date. The cores were kept together by a constant force of approximately 3lbs to avoid fracturing ferrite.

image-1656073841341.png

Image not found or type unknown

With this data, it can be seen that 0.0165" gets very close to the 720uH value called out in literature.

This data is important for determining engineering values such as instantaneous current, time constants for current curves, inductive reactance, etc.

EXAMPLE: Finding Inductive Reactance at 120Hz:

image-1656082086460.png

Image not found or type unknown

EXAMPLE: Finding Time constant of inductor:

image-1656082066204.png

Image not found or type unknown

EXAMPLE: Finding instantaneous current of inductor. t =time constant from above.

image-1656082132374.png

Image not found or type unknown

4200 Permeability EC52 E Core

The following test results were performed using a 4200 permeability EC52/24/14 core purchased from Surplus Sales. Please see the link below for the exact core.

[Surplus Sales 4200 EC52/24/14](#)

Magnetic's document covered the core material. 4200 permeability is listed within attached documentation.

[Magnetics_4200Core_Datasheet](#)

image-1656082760557.png

Image not found or type unknown

EC52/24/14 are the dimensions in mm. EC52 is called out in the component values given from Stan's estate data as seen below.

image-1656072073655.png

Image not found or type unknown

According to the above values, the inductance measured was 720uH per coil.

This being a bifilar coil, only one set needs measured. The replication winding methodology for this coil is covered by Max Miller in the below YouTube link. Please reference it to understand how the coils are wrapped.

[Ironmax How To Wind A 8XA ECore](#)

In the video, Max Miller mentions needing to gap the core. This reference is based off photos from Stan's estate provided by Don Gable. Below is a picture showing Stan's original gapped E core.

image-1656072716383.png

Image not found or type unknown

An LC meter was purchased to measure the values of inductances with precision plastic shims used for gapping. Plastic was selected to avoid any ferromagnetic materials affecting measurements.

Model number: LC100-A

Part Number: 021311199

image-1656072992165.png

Image not found or type unknown

The meter was tested with a known inductor purchased from Digikey. 33uH rating. Meter measured 35uH. This was acceptable for the measurements. To get a more precise measurement, a function generator and oscilloscope could be utilized. Below are the values of different gapping distances using the shims. Please note, that these are preliminary measurements. A better methodology is being worked on and will be available at a later date. The cores were kept together by a constant force of approximately 3lbs to avoid fracturing ferrite.

image-1656082965961.png

Image not found or type unknown

With this data, it can be seen that a higher permeability generates a higher inductance value. Therefore, a slightly larger gapping (using shims) would be required to match 720uH called out in literature.

This data is important for determining engineering values such as instantaneous current, time constants for current curves, inductive reactance, etc.

EXAMPLE: Finding Inductive Reactance at 120Hz:

image-1656082086460.png

Image not found or type unknown

EXAMPLE: Finding Time constant of inductor:

image-1656082066204.png

Image not found or type unknown

EXAMPLE: Finding instantaneous current of inductor. t =time constant from above.

image-1656082132374.png

Image not found or type unknown